

***TETRA - FOAM*****FOAM CLEANER FOR
DELICATE EQUIPMENT
AND ALUMINIUM SURFACES****APPLICATIONS:**

TETRA - FOAM especially used for foam wash
for delicate equipment and also in aluminium.

It has a wet and emulsifier power, it also eliminates
minerals, proteins and fats.

Surfaces are left sparkling clean and dry quickly, without remains.

Does not rust soft metals, such as Aluminium, Bronze, copper etc....

INSTRUCTIONS:

Use from 1 to 5 % with dispensers at low pressure

or with foam generators. Let it work

for about 10 min. and rinse with water at high pressure.

Safe on all metals.

COMPONENTS:

Silicates, non-ionic surfactants
alcohols, sequestering agents.

CHEMICAL - PHYSICAL DATA :

Status:	Liquid	Colour:	None
pH.:	11 conc.	Odour:	None
Foam:	High		

CAUTION :

Wear suitable clothes and gloves, protect eyes and face.

Corrosive. Causes severe burns. In case of contact with eyes or face,
rinse immediately with plenty of water and seek medical advice.